





Tubo de precisión rectangular



| Medidas | | Espesor medio (mm) | |
|---------|------|--------------------|---|
| (mm) | (mm) | 1,5 | 2 |
| 15 | 10 | | |
| 16 | 10 | | |
| 20 | 10 | | |
| 20 | 15 | | |
| 25 | 10 | | |
| 25 | 15 | | |
| 25 | 20 | | |
| 30 | 10 | | |
| 30 | 15 | | |
| 30 | 20 | | |
| 30 | 25 | | |
| 35 | 10 | | |
| 35 | 15 | | |
| 35 | 20 | | |
| 35 | 25 | | |
| 40 | 10 | | |
| 40 | 15 | | |
| 40 | 20 | | |
| 40 | 27 | | |
| 40 | 30 | | |
| 40 | 35 | | |
| 45 | 10 | | |
| 45 | 15 | | |
| 45 | 20 | | |
| 45 | 25 | | |
| 45 | 30 | | |
| 45 | 35 | | |
| 50 | 10 | | |
| 50 | 15 | | |
| 50 | 20 | | |
| 50 | 25 | | |
| 50 | 30 | | |
| 50 | 35 | | |
| 50 | 40 | | |
| 60 | 10 | | |
| 60 | 15 | | |
| 60 | 20 | | |
| 60 | 25 | | |
| 60 | 50 | | |



Tubo de precisión rectangular



| Medidas | | Espesor medio (mm) | |
|---------|------|--------------------|---|
| (mm) | (mm) | 1,5 | 2 |
| 70 | 20 | | |
| 70 | 25 | | |
| 70 | 30 | | |
| 70 | 40 | | |
| 70 | 50 | | |
| 80 | 20 | | |
| 80 | 30 | | |
| 80 | 40 | | |
| 80 | 50 | | |
| 80 | 60 | | |
| 90 | 30 | | |
| 90 | 40 | | |
| 90 | 50 | | |
| 100 | 20 | | |
| 100 | 30 | | |
| 100 | 40 | | |
| 100 | 50 | | |
| 100 | 60 | | |
| 100 | 80 | | |
| 120 | 40 | | |
| 120 | 60 | | |
| 120 | 80 | | |
| 140 | 60 | | |